



EL Class I

Date of issue: 11 August 2026

Valid until: 31 December 2027

EHEDG hereby declares that the product


***retractable assembly Cleanfit, type CPA875 (Code 'LC') with single service chamber
(Code '1', '2' or '3') with EPDM gaskets for 12 mm sensors***

from

Endress+Hauser Conducta GmbH+Co. KG, Dieselstrasse 24, 70839 GERLINGEN, Germany

*has/have been evaluated for compliance and meets/meet the current criteria for
Hygienic Equipment Design of closed process applications of the EHEDG*

Certificate No. EHEDG-C2600053

Signed  President EHEDG
Hein Timmerman

Signed  EHEDG Certification Officer
Karlijn Faber

EHEDG
Karspeldreef 8
1101 CJ Amsterdam
Netherlands

©EHEDG



APPENDIX 3

EHEDG Certification – Equipment Evaluation Form

Design Evaluation Date: 21.04.2026

EHEDG File Number: EHEDG-R2600045

Certification Type: EL CLASS I

Applicant: Endress+Hauser GmbH & Co. KG

Equipment: retractable assembly Cleanfit, type CPA875 (Code 'LC') with single service chamber (Code '1', '2' or '3') with EPDM gaskets for 12 mm sensors

Other essential identification: for EHEDG certified sensors

Evaluated by:

Name: Dr. Jürgen Hofmann

Date, Signature: 20.07.2026

Approved by:

Name: Irene Llorca

20006744X
MARIA IRENE
LLORCA
(C:G46421988)Firmado digitalmente por
20006744X MARIA IRENE
LLORCA (C:G46421988)
Fecha: 2026.07.24
09:46:29 +02'00'

Date, Signature: _____

The use of the EHEDG Certification logo is justified based on the results of the design evaluation, inspection, and testing (as applicable) of the equipment for compliance with the current EHEDG Hygienic Design Criteria (HDC):

Criteria	Certification for use in Closed Processes
☐	The equipment complies with all applicable HDC in the Guidelines.
☒	Evidence for compliance required and provided by in-place cleanability test method according to EHEDG Doc. 2.
☐	Evidence for compliance required and provided by in-place cleanability test method according to EHEDG Doc. 2, in-place sterilisability test method according to EHEDG Doc. 5, and bacteria tightness test according to EHEDG Doc. 7 for EL ASEPTIC Certification.
Criteria	Certification for use in Open Processes
☐	The equipment complies with all applicable HDC in the Guidelines.
☐	Evidence for compliance required and provided by OPC cleanability test method according to EHEDG Doc. 57.

APPENDIX 3

No.	Description
1.	EHEDG Certificate of Compliance
2.	Contract to use the EHEDG Certification Logo for equipment
3.	Appendix 1: Equipment intended for cleaning-in-place with liquids without dismantling
4.	Appendix 2: Conditions for use of the EHEDG Certification Logo
5.	Appendix 3: Equipment evaluation form
6.	Evaluation report of the design of the retractable assembly Cleanfit, type CPA875 (Code 'LC') with single service chamber (Code '1', '2' or '3') with EPDM gaskets for 12 mm sensors, no. 710TUM2026
7.	Drawings of the retractable assembly Cleanfit, type CPA875 (Code 'LC') with single service chamber (Code '1', '2' or '3') with EPDM gaskets for 12 mm sensors, drawing nos. 961004997, 211049876, 211050308, 211050292 (page 1 of 2), 211050015, 401825; original stamped
8.	Test report of the in-place cleanability test method according to Doc. 2, Test no. 710/22.09.2020.
9.	Cleaning and Installation manual (excerpt) nos. BA01279C/07/EN/06.26-00 supplied by the manufacturer
10.	Example of EHEDG Certified Logo Type EL CLASS I