

CERTIFICATE OF COMPLIANCE



EL Class I

Date of issue: 24 September 2026

Valid until: 31 December 2027


EHEDG hereby declares that the product
oxygen sensor, type OXY 5100 with FKM O-ring and silicone or PTFE diaphragm

from

Anton Paar GmbH, 20 Anton-Paar-Str, 8054 GRAZ, Austria

has/have been evaluated for compliance and meets/meet the current criteria for
Hygienic Equipment Design of closed process applications of the EHEDG

Certificate No. EHEDG-C2600057

Signed  *President EHEDG*
Hein Timmerman

Signed  *EHEDG Certification Officer*
Karlijn Faber

EHEDG
Karspeldreef 8
1101 CJ Amsterdam
Netherlands

©EHEDG



APPENDIX 3 EHEDG Certification – Equipment Evaluation Form

Design Evaluation Date: 16.07.2026

EHEDG File Number: EHEDG-R2600008

Certification Type: EL CLASS I

Applicant: Anton Paar GmbH

Equipment: oxygen sensor, type OXY 5100 with FKM O-ring and silicone or PTFE diaphragm

Other essential identification:

Evaluated by:

Name: Dr. Jürgen Hofmann

Date, Signature: 08.09.2026

Approved by:

Name: Mark Morgan

Date, Signature: 08.09.2026

The use of the EHEDG Certification logo is justified based on the results of the design evaluation, inspection, and testing (as applicable) of the equipment for compliance with the current EHEDG Hygienic Design Criteria (HDC):

Criteria	Certification for use in Closed Processes
☐	The equipment complies with all applicable HDC in the Guidelines.
☒	Evidence for compliance required and provided by in-place cleanability test method according to EHEDG Doc. 2.
☐	Evidence for compliance required and provided by in-place cleanability test method according to EHEDG Doc. 2, in-place sterilisability test method according to EHEDG Doc. 5, and bacteria tightness test according to EHEDG Doc. 7 for EL ASEPTIC Certification.
Criteria	Certification for use in Open Processes
☐	The equipment complies with all applicable HDC in the Guidelines.
☐	Evidence for compliance required and provided by OPC cleanability test method according to EHEDG Doc. 57.

APPENDIX 3

No.	Description
1.	EHEDG Certificate of Compliance
2.	Contract to use the EHEDG Certification Logo for equipment
3.	Appendix 1: Equipment intended for cleaning-in-place with liquids without dismantling
4.	Appendix 2: conditions for use of the EHEDG Certification Logo
5.	Appendix 3: Equipment evaluation form
6.	Evaluation report of the design of the oxygen sensor, type OXY 5100 with FKM O-ring and silicone or PTFE diaphragm, no. 728TUM2026
7.	Drawings of the oxygen sensor, type OXY 5100 with FKM O-ring and silicone or PTFE diaphragm, drawing nos. D25MZ0150_EHEDG Rev. 5, D25M00204 Rev. B; original stamped
8.	Test reports of the in-place cleanability test method according to Doc. 2, Test nos. 651/21.09.2018 and 728/24.03.2021
9.	Cleaning and Installation manual (excerpt) no. D25IB002EN-F supplied by the manufacturer
10.	Example of EHEDG Certified Logo Type EL CLASS I