



Date of issue: 4 December 2018

Valid until end: December 2020

EL Class I

EHEDG hereby declares that the product


Lobe Positive Displacement Pump, type C series with EPDM gaskets


from

OMAC S.r.l., Via G. Falcone, 8, I-42048 Rubiera (RE), Italy

*has/have been evaluated for compliance and meets/meet the current criteria for
Hygienic Equipment Design of the EHEDG*

Certificate No. EHEDG-C1800034

Signed  _____ *President EHEDG*
Ludvig Joesefsberg

Signed  _____ *EHEDG Certification Officer*
Mirjam Steenaard

*EHEDG Secretariat
Lyoner Straße 18
60528 Frankfurt am Main
Germany*

©EHEDG



Appendix 3

EHEDG Certification – Equipment Evaluation Form

Date: 04.12.2018

EHEDG File Number: EHEDG-C1800034

Certification Type: EL CLASS I

Applicant: OMAC SRL, RUBIERA ITALY

Equipment: Lobe positive displacement pump

Type or model No/s.: Type C sizes C100, C110, C115, C220, C270, C330

Other essential identification: with EPDM gaskets and silicon carbide mechanical seals

Evaluated by:

Name: Giampaolo BETTA [AEO]

Approved by:

Name: Nicolas ROSSI

Title: [AEO]

Date, Signature: 10/12/18 

<p>1. Results of inspection for compliance with the EHEDG Hygienic Design Criteria. Conclusion: The equipment complies with the criteria. The use of the EHEDG Certification logo is justified:</p>	<p>YES <input type="checkbox"/></p> <p>MAYBE <input checked="" type="checkbox"/></p>
<p>2. Evidence for compliance provided and convincing for Certification. Conclusion: The equipment complies with the criteria where possible. The use of the EHEDG Certification logo is justified:</p>	<p>YES <input checked="" type="checkbox"/></p>

Signature: 

Date: 04/12/2018

The original of this form will be kept by EHEDG together with the application, the inspection report, the evidence provided and any other relevant documentation, as listed on the back.

Appendix 3

No.	Description
1	EHEDG Certificate of Compliance
2	Contract to use the EHEDG Certification Logo for equipment
3	Appendix 1: Equipment intended for cleaning in place with liquids without dismantling
4	Appendix 2: Conditions for use of the EHEDG Certification Logo
5	Appendix 3: Equipment evaluation form
6	EHEDG hygienic design criteria evaluation report 2018DRGB002
7	Drawings of the Lobe pump type C sizes C100, C110, C115, C220, C270, C330 with EPDM gaskets and silicon carbide mechanical seals – Drawings numbers SC-323, SC-324, SC-325, SC-326, SC-327, SC-328 - Original stamped
8	Test report no. 155/25.01.2008 – EHEDG 01 Cleanability Test lobe positive displacement pump, series C220
9	Example Logo EL class I

The original of this form will be kept by EHEDG together with the application, the inspection report, the evidence provided and any other relevant documentation, as listed on the back.