

CERTIFICATE OF COMPLIANCE



Date of issue: 11 November 2019

Valid until: 31 December 2020

EL Class I

EHEDG hereby declares that the product

optical In-line Spectrometer Memosens Wave CKI50 with PEEK profiled gaskets and FFKM sealing

from

Endress+Hauser Conducta GmbH+Co. KG, Dieselstrasse 24 , 70839 Gerlingen, Germany

has/have been evaluated for compliance and meets/meet the current criteria for Hygienic Equipment Design of the EHEDG

Certificate No. EHEDG-C1900174

Signed

Ludvig Josefsberg

President EHEDG

Signed

Mirjam Steenaard

EHEDG Certification Officer

*EHEDG Secretariat
Lyoner Straße 18
60528 Frankfurt am Main
Germany*

©EHEDG



Appendix 3

EHEDG Certification – Equipment Evaluation Form

Date: 31.07.2019

EHEDG File Number: EHEDG-C1900174

Certification Type: EL CLASS I

Applicant: Endress+Hauser Conducta GmbH+Co. KG

Equipment: Optical In-line Spectrometer

Type or model No/s.: Memosens Wave CKI50 with PEEK profiled gaskets and FFKM sealing

Other essential identification: 2 mm, 5 mm, 10 mm path length

Evaluated by:

Name: Dr. Jürgen Hofmann

Approved by:

Name: Shih Rong Huang

Title: [AEO]

Date, Signature: Willy Shih-Rong Huang 10.12.2019

1. Results of inspection for compliance with the EHEDG Hygienic Design Criteria.

Conclusion:

The equipment complies with the criteria.

YES

The use of the EHEDG Certification logo is justified:

MAYBE

2. Evidence for compliance provided and convincing for Certification.

Conclusion:

The equipment complies with the criteria where possible.

YES

The use of the EHEDG Certification logo is justified:

Signature: J. Hofmann

Date: 11.11.2019

The original of this form will be kept by EHEDG together with the application, the inspection report, the evidence provided and any other relevant documentation, as listed on the back.

Appendix 3

No.	Description
1.	EHEDG Certificate of Compliance
2.	Contract to use the EHEDG Certification Logo for equipment
3.	Appendix 1: Equipment intended for cleaning-in-place with liquids without dismantling
4.	Appendix 2: conditions for use of the EHEDG Certification Logo
5.	Appendix 3: Equipment evaluation form
6.	Evaluation report of the design of the optical In-line Spectrometer Memosens Wave CKI50 with PEEK profiled gaskets and FFKM sealing, no. 676TUM2019
7.	Drawings of the optical In-line Spectrometer Memosens Wave CKI50 with PEEK profiled gaskets and FFKM sealing, drawing no. 433460 original stamped
8.	Test report of the in-place cleanability test method, no. 676/20.05.2019
9.	Example of EHEDG Certified Logo Type EL CLASS I