EHELO.

EL Class I

Date of issue: 19 December 2020

Valid until: 31 December 2023

EHEDG hereby declares that the product

### pH-sensor type InProX1 HLS-A200-Bxxx installed with sensor fitting InFit761

from

Mettler Toledo GmbH, Im Hackacker 15, 8902 Urdorf, Switzerland

has/have been evaluated for compliance and meets/meet the current criteria for Hygienic Equipment Design of the EHEDG

## Certificate No. EHEDG-C2000082

Signed \_

Ludvig Josefsberg

President EHEDG

Signed

Karlijn Faber

EHEDG Certification Officer

EHEDG Gooimeer 1 1411 DC Naarden Netherlands

©EHEDG



#### Appendix 3

## **EHEDG Certification – Equipment Evaluation Form**

Design Evaluation Date: 09.11.2020

EHEDG File Number: EHEDG-C2000082

Certification Type: EL CLASS I

Applicant:	Mottlor		Cmh
Applicant.	Mettlei-	oleuo	GIIIDI I

Equipment: pH-sensor type InProX1 HLS-A200-Bxxx installed with sensor fitting InFit761

Other essential identification:

Evaluated by:

Name: Dr. Jürgen Hofmann

Approved by:

Name: Rafa Soro

Title: AEO

Date, Signature: \_\_\_\_\8. \2. 7070

1.	Results of inspection for compliance with the EHEDG Hygienic Design Criteria.
	Conclusion:

The equipment complies with the criteria.

The use of the EHEDG Certification logo is justified:

YES □ MAYBE ☑

2. Evidence for compliance provided and convincing for Certification.

Conclusion:

The equipment complies with the criteria where possible.

The use of the EHEDG Certification logo is justified:

Mafin am

YES 🗹

Signature:

Date: 14.12.2020

The original of this form will be kept by EHEDG together with the application, the inspection report, the evidence provided and any other relevant documentation, as listed on the back.

# Appendix 3

No.	Description
1.	EHEDG Certificate of Compliance
2.	Contract to use the EHEDG Certification Logo for equipment
3.	Appendix 1: Equipment intended for cleaning-in-place with liquids without dismantling
4.	Appendix 2: conditions for use of the EHEDG Certification Logo
5.	Appendix 3: Equipment evaluation form
6.	Evaluation report of the design of the pH-sensor type InProX1 HLS-A200-Bxxx installed with sensor fitting InFit761, no. 11020TUM2020
7.	Drawing of the pH-sensor type InProX1 HLS-A200-Bxxx installed with sensor fitting InFit761, drawing nos. d000195848-B; original stamped
8.	Test report of the in-place cleanability test method, 17-P00036
9.	Cleaning and Installation manual provided by the equipment supplier
10.	Example of EHEDG Certified Logo Type EL CLASS I