

# CERTIFICATE OF COMPLIANCE



**EL Class I**

*Date of issue: 8 October 2024*

*Valid until: 31 December 2025*

*EHEDG hereby declares that the product  
conductivity meters, type ILM-4 and ILM-4R made of PEEK with CLEANadapt “G1”  
hygienic (Code “S01”)*

*from*

*Negele Messtechnik GmbH, Raiffeisenweg 7, 87743 Egg an der Günz, Germany*

*has/have been evaluated for compliance and meets/meet the current criteria for  
Hygienic Equipment Design of closed process applications of the EHEDG*


***Certificate No. EHEDG-C2400046***

Signed \_\_\_\_\_ *Hein Timmerman* \_\_\_\_\_ *President EHEDG*

Signed \_\_\_\_\_ *Karlijn Faber* \_\_\_\_\_ *EHEDG Certification Officer*

*EHEDG  
Karspeldreef 8  
1101 CJ Amsterdam  
Netherlands*

©EHEDG



### APPENDIX 3

## EHEDG Certification – Equipment Evaluation Form

Design Evaluation Date: 12.01.2024

EHEDG File Number: EHEDG-R2400047

Certification Type: EL CLASS I

Applicant: Negele Messtechnik GmbH

Equipment: conductivity meters, type ILM-4 and ILM-4R made of PEEK with CLEANadapt "G1" hygienic (Code "S01")

Other essential identification: process adapter DIN 32676 in sizes DN40, DN50, DN65 and 1 1/2", 2", 2 1/2", 3" (Code "AMC-351") and VARINLINE type N in size DN40 and F in size DN25 (Codes "AMV-351/DN40" and "AMV-351/DN25"), weld-in adapter (Codes "EMS-351" and "EMZ-351"), build-in system (Code "EHG-DIN2-xx/1"-L)

**Evaluated by:**

Name: Dr. Jürgen Hofmann

Date, Signature: 27.09.2024

**Approved by:**

Name: Jacques Kastelein

Date, Signature: \_\_\_\_\_

29/10.2024

The use of the EHEDG Certification logo is justified based on the results of the design evaluation, inspection, and testing (as applicable) of the equipment for compliance with the current EHEDG Hygienic Design Criteria (HDC):

Criteria	Certification for use in Closed Processes
<input type="checkbox"/>	The equipment complies with all applicable HDC in the Guidelines.
<input checked="" type="checkbox"/>	Evidence for compliance required and provided by in-place cleanability test method according to EHEDG Doc. 2.
<input type="checkbox"/>	Evidence for compliance required and provided by in-place cleanability test method according to EHEDG Doc. 2, in-place sterilisability test method according to EHEDG Doc. 5, and bacteria tightness test according to EHEDG Doc. 7 for <b>EL ASEPTIC</b> Certification.
Criteria	Certification for use in Open Processes
<input type="checkbox"/>	The equipment complies with all applicable HDC in the Guidelines.
<input type="checkbox"/>	Evidence for compliance required and provided by OPC cleanability test method according to EHEDG Doc. 57.



### APPENDIX 3

No.	Description
1.	EHEDG Certificate of Compliance
2.	Contract to use the EHEDG Certification Logo for equipment
3.	Appendix 1: Equipment intended for cleaning-in-place with liquids without dismantling
4.	Appendix 2: conditions for use of the EHEDG Certification Logo
5.	Appendix 3: Equipment evaluation form
6.	Evaluation report of the design of the conductivity meters, type ILM-4 and ILM-4R made of PEEK with CLEANadapt “G1” hygienic (Code “S01”), no. 610TUM2024
7.	Drawings of the conductivity meters, type ILM-4 and ILM-4R made of PEEK with CLEANadapt “G1” hygienic (Code “S01”), Drawing nos. B57.774110/20, B537135xx-E, B53-71353x-C, 60xx-0305, B53.713541-B, B53.713548-C; original stamped
8.	Test report of the in-place cleanability test method according to Doc. 2, Test no. 610/07.11.2017.
9.	Cleaning and Installation manual nos.50144/1.2.3/2024-08-20/AS and 50000/5.0.1/2024-08-20/MH/NA-EU supplied by the manufacturer
10.	Example of EHEDG Certified Logo Type EL CLASS I