



EL Class I

Date of issue: 4 February 2026

Valid until: 31 December 2027

EHEDG hereby declares that the product

Top Wing rotary lobe pump series TW1/0041, TW1/0082, TW2/0171, TW2/0343, TW3/0537, TW3/1100, TW4/1629, TW4/3257 with EPDM or FPM gaskets and SiC or C mechanical seal material

from

SPX FLOW Technology Poland sp. z o.o., Rolbieskiego 2, 85-862 BYDGOSZCZ, Poland

has/have been evaluated for compliance and meets/meet the current criteria for Hygienic Equipment Design of closed process applications of the EHEDG

Certificate No. EHEDG-C2600005

Signed  President EHEDG
Hein Timmerman

Signed  EHEDG Certification Officer
Karlijn Faber

EHEDG
Karspeldreef 8
1101 CJ Amsterdam
Netherlands

©EHEDG



APPENDIX 3

EHEDG Certification – Equipment Evaluation Form

Design Evaluation Date: 25.03.2025

EHEDG File Number: EHEDG-R2500087

Certification Type: EL CLASS I

Applicant: SPX FLOW TECHNOLOGY POLAND Sp. z o.o.

Equipment: TopWing rotary lobe pump series TW1/0041, TW1/0082, TW2/0171, TW2/0343, TW3/0537, TW3/1100, TW4/1629, TW4/3257 with EPDM or FPM gaskets and SiC or C mechanical seal material

Other essential identification:

Evaluated by:

Name: Dr. Jürgen Hofmann

Date, Signature: 15.01.2026

Approved by:

Name: Irene Llorca

Date, Signature: _____

20006744X
MARIA IRENE LLORCA
LLORCA
(C:G46421988)
Firmado digitalmente
por 20006744X
MARIA IRENE LLORCA
(C:G46421988)
Fecha: 2026.02.02
07:58:17 +01'00'

The use of the EHEDG Certification logo is justified based on the results of the design evaluation, inspection, and testing (as applicable) of the equipment for compliance with the current EHEDG Hygienic Design Criteria (HDC):

Criteria	Certification for use in Closed Processes
<input type="checkbox"/>	The equipment complies with all applicable HDC in the Guidelines.
<input checked="" type="checkbox"/>	Evidence for compliance required and provided by in-place cleanability test method according to EHEDG Doc. 2.
<input type="checkbox"/>	Evidence for compliance required and provided by in-place cleanability test method according to EHEDG Doc. 2, in-place sterilisability test method according to EHEDG Doc. 5, and bacteria tightness test according to EHEDG Doc. 7 for EL ASEPTIC Certification.
Criteria	Certification for use in Open Processes
<input type="checkbox"/>	The equipment complies with all applicable HDC in the Guidelines.
<input type="checkbox"/>	Evidence for compliance required and provided by OPC cleanability test method according to EHEDG Doc. 57.

APPENDIX 3

No.	Description
1.	EHEDG Certificate of Compliance
2.	Contract to use the EHEDG Certification Logo for equipment
3.	Appendix 1: Equipment intended for cleaning-in-place with liquids without dismantling
4.	Appendix 2: conditions for use of the EHEDG Certification Logo
5.	Appendix 3: Equipment evaluation form
6.	Evaluation report of the design of the TopWing rotary lobe pump series TW1/0041, TW1/0082, TW2/0171, TW2/0343, TW3/0537, TW3/1100, TW4/1629, TW4/3257 with EPDM or FPM gaskets and SiC or C mechanical seal material, no. 810TUM2025
7.	Drawings of the TopWing rotary lobe pump series TW1/0041, TW1/0082, TW2/0171, TW2/0343, TW3/0537, TW3/1100, TW4/1629, TW4/3257 with EPDM or FPM gaskets and SiC or C mechanical seal material, drawing nos. TWC-00000V1, TWC-00000V2, TWC-00000V3; original stamped
8.	Test report of the in-place cleanability test method according to Doc. 2, Test nos. 657/20.11.2018, 810/08.04.2025.
9.	Cleaning and Installation manual (excerpt) no. A.0500.301 – IM-TW/16.00EN supplied by the manufacturer
10.	Example of EHEDG Certified Logo Type EL CLASS I